



# TownGuide Performer

## BDP103 LED30/830 DW PCF SI CLO 62P

TOWNGUIDE PERF CLASSIC T, LED GreenLine 3000 lm, Distribution wide, Polycarbonate bowl/cover frosted, Constant light output, Post-top for diameter 62 mm

The TownGuide Performer family consists of six recognizable yet modern shapes: Flat Cone, Bowl, Classic Cone, Classic, T and Tzero. All are available with a clear bowl. Except for Tzero, also a frosted bowl can be chosen. With an extensive range of lumen packages and a choice of light colors and operating lifetimes, it is easy to select the version that best suits your project's specific requirements. In addition, TownGuide Performer has a variety of control system options that can make it an integral part of your smart energy-reduction programs – from stand-alone LumiStep and DynaDimmer, SDU switch-dim control, through to seamless remote connectivity with CityTouch lighting management software. Installation is easy. Thanks to the bayonet whistle connector with integrated gland located in the spigot, the luminaire does not have to be opened at all for installation. Philips has made every effort to make the Total Cost of Ownership (TCO) of the luminaire as attractive as possible. And as TownGuide Performer is a dedicated LED luminaire, compatible with a variety of control systems, the energy and maintenance cost savings compared to conventional lighting are significant.

### Product data

General Information		Product family code	BDP103 [TOWNGUIDE PERF CLASSIC T]
Lamp family code	GRN30 [LED GreenLine 3000 lm]	Lighting Technology	LED
Light source replaceable	Yes	Value ladder	Performance
Number of gear units	1 unit	Embedded control	Constant light output
Driver included	Yes	CE mark	Yes
Photocell	-	Warranty period	5 years
Light source engine type	LED	Flammability mark	-

# TownGuide Performer

ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	No

## Light Technical

Upward light output ratio	0.4
Luminous Flux	1,450 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	63 lm/W
Color rendering index (CRI)	80
Number of light sources	4
Light source color	830 warm white
Optical cover type	Polycarbonate bowl/cover frosted
Luminaire light beam spread	50° x 70°
Optic type outdoor	Distribution wide

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	23 W
Average CLO power consumption	23.5 W
End CLO power consumption	23.5 W
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	23.5 W
Power Factor (Fraction)	0.97
Connection	Screw connection block 5-pole
Cable	-
Number of products on MCB of 16 A type B 20	

## Temperature

Ambient temperature range	-40 to +35 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating with constant light output
Control interface	-
Constant light output	Yes

## Mechanical and Housing

Housing Material	Aluminum
------------------	----------

Reflector material	-
Optic material	Acrylate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Silver
Mounting device	Post-top for diameter 62 mm
Optical cover shape	Wide
Optical cover finish	Frosted
Overall height	458 mm
Overall diameter	570 mm
Effective projected area	0.093 m <sup>2</sup>
Parts color	All parts colored

## Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

## Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
-------------------------------	-------

## Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

## Product Data

Order product name	BDP103 LED30/830 DW PCF SI CLO 62P
Full product name	BDP103 LED30/830 DW PCF SI CLO 62P
Full product code	871829191076300
Order code	910500991137
Material Nr. (12NC)	910500991137
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291910763
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291910763

## TownGuide Performer

### Dimensional drawing

