



TBH375

TBH375 2xTL-D58W HFR PI

TBH375, 2, MASTER TL-D, 58 W, HF Regulator, Push-in connector 3-pole


Ball-impact-resistant luminaire for TL-D fluorescent lamps, specially designed for multipurpose sports halls and tennis halls. Lamellae prevent players from seeing directly into the lamps. Strong housing construction protects lamps against ball impact. For surface or recessed mounting. Optics supplied with the luminaire.

Product data

General Information		Protection class IEC		Safety class I	
Lamp family code	TL-D [MASTER TL-D]				
Gear	HFR [HF Regulator]				
Product family code	TBH375 [TBH375]				
CE mark	Yes				
ENEC mark	ENEC mark				
Light Technical		Application Conditions			
Number of light sources	2	Suitable for random switching	Not applicable		
Operating and Electrical		Product Data			
Input Voltage	220 to 240 V	Order product name	TBH375 2xTL-D58W HFR PI		
Power Consumption	58 W	Full product name	TBH375 2xTL-D58W HFR PI		
Connection	Push-in connector 3-pole	Full product code	871155963563700		
Mechanical and Housing		Order code	910501138103		
Overall width	313 mm	Material Nr. (12NC)	910501138103		
Approval and Application		Numerator - Quantity Per Pack	1		
Ingress protection code	IP20 [Finger-protected]	EAN/UPC - Product/Case	8711559635637		
		Numerator - Packs per outer box	1		
		EAN/UPC - Case	8711559635637		

TBH375

Dimensional drawing



Product

TBH375 2xTL-D58W HFR PI

