



Arano TPS640/642/644

TPS640 2x28W/840 HFP C8 SMS ALU

ARANO, 2, 28 W, 840 neutral white, HF Performer, High-gloss optic 3D micro-lamellae, Aluminum

Arano is a range of luminaires for TL5 fluorescent lamps and LED light sources, featuring Philips' micro-optics. The patented micro-optic with 3D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully in compliance with the latest office-lighting norm (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

Product data

General Information		Optic type	
Lamp family code	TL5 [TL5]	Optical cover type	-
Gear	HFP [HF Performer]	Operating and Electrical	
Product family code	TPS640 [ARANO]	Input Voltage	230 to 240 V
Embedded control	-	Power Consumption	28 W
CE mark	Yes	Cable	-
Flammability mark	For mounting on normally flammable surfaces	Mechanical and Housing	
ENEC mark	ENEC mark	Housing Color	Aluminum
Glow-wire test	Temperature 850 °C, duration 5 s	Approval and Application	
Light Technical		Ingress protection code	IP20 [Finger-protected]
Number of light sources	2		
Light source color	840 neutral white		

Arano TPS640/642/644

Protection class IEC	Safety class I
----------------------	----------------

Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------

Product Data

Order product name	TPS640 2x28W/840 HFP C8 SMS ALU
Full product name	TPS640 2x28W/840 HFP C8 SMS ALU
Full product code	871155974610400

Order code	910501234903
------------	--------------

Material Nr. (12NC)	910501234903
---------------------	--------------


Numerator - Quantity Per Pack	1
-------------------------------	---

EAN/UPC - Product/Case	8711559746104
------------------------	---------------

Numerator - Packs per outer box	1
---------------------------------	---

EAN/UPC - Case	8711559746104
----------------	---------------

Dimensional drawing



Product

TPS640 2x28W/840 HFP C8 SMS ALU

