



Arano TCS640

TCS640 2x28W/830 HFP M2 ALU

ARANO, 2, 28 W, 830 warm white, HF Performer, Matt mirror ribbed lamellae louver, Aluminum

Arano is a range of luminaires for TL5 fluorescent lamps and LED light sources, featuring Philips' micro-optics. The patented micro-optic with 3-D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully compliant with the current norm for indoor working places (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

Product data



General Information		Optical cover type	
Lamp family code	TL5 [TL5]	-	
Gear	HFP [HF Performer]	Operating and Electrical	
Product family code	TCS640 [ARANO]	Power Consumption	28 W
Embedded control	-	Cable	-
CE mark	Yes	Mechanical and Housing	
Flammability mark	For mounting on normally flammable surfaces	Housing Color	Aluminum
ENEC mark	ENEC mark	Approval and Application	
Glow-wire test	Temperature 960 °C, duration 5 s	Ingress protection code	IP20 [Finger-protected]
Light Technical		Protection class IEC	Safety class I
Number of light sources	2		
Light source color	830 warm white		
Optic type	Matt mirror ribbed lamellae louver		

Arano TCS640

Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TCS640 2x28W/830 HFP M2 ALU
Full product name	TCS640 2x28W/830 HFP M2 ALU
Full product code	871155974877100
Order code	910501260603

Material Nr. (12NC)	910501260603
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559748771
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559748771

Dimensional drawing



Product
TCS640 2x28W/830 HFP M2 ALU

