



Arano

TPS640/642/644

TPS642 1x54W/830 HFR D8 SM2 ALU

ARANO, 1, 54 W, 830 warm white, HF Regulator, Semi-high-gloss optic 3D micro-lamellae, Aluminum

Arano is a range of luminaires for TL5 fluorescent lamps and LED light sources, featuring Philips' micro-optics. The patented micro-optic with 3D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully in compliance with the latest office-lighting norm (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

Product data



General Information		Optic type	
Lamp family code	TL5 [TL5]	Optical cover type	-
Gear	HFR [HF Regulator]	Operating and Electrical	
Product family code	TPS642 [ARANO]	Input Voltage	230 to 240 V
Embedded control	-	Power Consumption	54 W
CE mark	Yes	Cable	-
Flammability mark	For mounting on normally flammable surfaces	Mechanical and Housing	
ENEC mark	ENEC mark	Housing Color	Aluminum
Glow-wire test	Temperature 850 °C, duration 5 s	Approval and Application	
Light Technical		Ingress protection code	IP20 [Finger-protected]
Number of light sources	1		
Light source color	830 warm white		

Arano TPS640/642/644

Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TPS642 1x54W/830 HFR D8 SM2 ALU
Full product name	TPS642 1x54W/830 HFR D8 SM2 ALU
Full product code	871155974969300

Order code	910501269803
Material Nr. (12NC)	910501269803
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559749693
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559749693

Dimensional drawing



Product
TPS642 1x54W/830 HFR D8 SM2 ALU

