



Arano TCS640

TCS640 2x28W/840 HFP AC-MLO ALU

ARANO, 2, 28 W, 840 neutral white, HF Performer, Acrylate micro-lens optic, Aluminum

Arano is a range of luminaires for TL5 fluorescent lamps and LED light sources, featuring Philips' micro-optics. The patented micro-optic with 3-D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully compliant with the current norm for indoor working places (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

Product data



General Information		Optical cover type		Acrylate micro-lens optic
Lamp family code	TL5 [TL5]			
Gear	HFP [HF Performer]			
Product family code	TCS640 [ARANO]	Operating and Electrical		
Embedded control	-	Power Consumption	28 W	
CE mark	Yes	Cable	-	
Flammability mark	For mounting on normally flammable surfaces	Mechanical and Housing		
ENEC mark	ENEC mark	Optical cover material	Acrylate	
Glow-wire test	Temperature 650 °C, duration 5 s	Fixation point length distance (Nom)	1,000 mm	
		Housing Color	Aluminum	
Light Technical		Approval and Application		
Number of light sources	2	Ingress protection code	IP40 [Wire-protected]	
Light source color	840 neutral white	Protection class IEC	Safety class I	
Optic type	-			

Arano TCS640

Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TCS640 2x28W/840 HFP AC-MLO ALU
Full product name	TCS640 2x28W/840 HFP AC-MLO ALU
Full product code	871155975012500
Order code	75012500

Material Nr. (12NC)	910501273803
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559750125
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559750125

Dimensional drawing



Product
TCS640 2x28W/840 HFP AC-MLO ALU

