



# Arano TCS640

## TCS640 1x35W/830 HFP AC-MLO ALU

ARANO, 1, 35 W, 830 warm white, HF Performer, Acrylate micro-lens optic, Aluminum

Arano is a range of luminaires for TL5 fluorescent lamps and LED light sources, featuring Philips' micro-optics. The patented micro-optic with 3-D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully compliant with the current norm for indoor working places (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

### Product data


General Information		Optical cover type	
Lamp family code	TL5 [TL5]	Acrylate micro-lens optic	
Gear	HFP [HF Performer]	Operating and Electrical	
Product family code	TCS640 [ARANO]	Power Consumption	35 W
Embedded control	-	Cable	-
CE mark	Yes	Mechanical and Housing	
Flammability mark	For mounting on normally flammable surfaces	Fixation point length distance (Nom)	1,300 mm
ENEC mark	ENEC mark	Housing Color	Aluminum
Glow-wire test	Temperature 650 °C, duration 5 s	Approval and Application	
Light Technical		Ingress protection code	IP40 [Wire-protected]
Number of light sources	1	Protection class IEC	Safety class I
Light source color	830 warm white		
Optic type	-		

Arano TCS640

Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TCS640 1x35W/830 HFP AC-MLO ALU
Full product name	TCS640 1x35W/830 HFP AC-MLO ALU
Full product code	871155975220400
Order code	910501290003

Material Nr. (12NC)	910501290003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559752204
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559752204

Dimensional drawing



Product
TCS640 1x35W/830 HFP AC-MLO ALU

