



Arano TCS640

TCS640 2x49W/840 HFP C8-VH ALU

ARANO, 2, 49 W, 840 neutral white, HF Performer, High-gloss optic 3D micro-lamellae very high reflectance, Aluminum

Arano is a range of luminaires for TL5 fluorescent lamps and LED light sources, featuring Philips' micro-optics. The patented micro-optic with 3-D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully compliant with the current norm for indoor working places (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

Product data


General Information		Optical cover type	
Lamp family code	TL5 [TL5]	-	
Gear	HFP [HF Performer]	Operating and Electrical	
Product family code	TCS640 [ARANO]	Power Consumption	49 W
Embedded control	-	Cable	-
CE mark	Yes	Mechanical and Housing	
Flammability mark	For mounting on normally flammable surfaces	Fixation point length distance (Nom)	1,300 mm
ENEC mark	ENEC mark	Housing Color	Aluminum
Glow-wire test	Temperature 960 °C, duration 5 s	Approval and Application	
Light Technical		Ingress protection code	IP20 [Finger-protected]
Number of light sources	2	Protection class IEC	Safety class I
Light source color	840 neutral white		
Optic type	High-gloss optic 3D micro-lamellae very high reflectance		

Arano TCS640

Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TCS640 2x49W/840 HFP C8-VH ALU
Full product name	TCS640 2x49W/840 HFP C8-VH ALU
Full product code	871155975513700
Order code	910501313703

Material Nr. (12NC)	910501313703
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559755137
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559755137

Dimensional drawing



Product
TCS640 2x49W/840 HFP C8-VH ALU

