



Arano TCS640

TCS640 4x14W/840 HFP C8-VH ALU

ARANO, 4, 14 W, 840 neutral white, HF Performer, High-gloss optic 3D micro-lamellae very high reflectance, Aluminum

Arano is a range of luminaires for TL5 fluorescent lamps and LED light sources, featuring Philips' micro-optics. The patented micro-optic with 3-D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully compliant with the current norm for indoor working places (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

Product data

General Information		Optical cover type		-
Lamp family code	TL5 [TL5]			
Gear	HFP [HF Performer]			
Product family code	TCS640 [ARANO]	Operating and Electrical		
Embedded control	-	Power Consumption	14 W	
CE mark	Yes	Cable	-	
Flammability mark	For mounting on normally flammable surfaces	Mechanical and Housing		
ENEC mark	ENEC mark	Housing Color	Aluminum	
Glow-wire test	Temperature 960 °C, duration 5 s	Approval and Application		
Light Technical		Ingress protection code	IP20 [Finger-protected]	
Number of light sources	4	Protection class IEC	Safety class I	
Light source color	840 neutral white			
Optic type	High-gloss optic 3D micro-lamellae very high reflectance			

Arano TCS640

Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TCS640 4x14W/840 HFP C8-VH ALU
Full product name	TCS640 4x14W/840 HFP C8-VH ALU
Full product code	871155975526700
Order code	910501315003

Material Nr. (12NC)	910501315003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559755267
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559755267

Dimensional drawing

