

# Arano

## TPS640/642/644

### TPS642 2x49W/840 HFP M2 SMS ALU

ARANO, 2, 49 W, 840 neutral white, HF Performer, Matt mirror ribbed lamellae louver, Aluminum

Arano is a range of luminaires for TL5 fluorescent lamps and LED light sources, featuring Philips' micro-optics. The patented micro-optic with 3D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully in compliance with the latest office-lighting norm (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

#### Product data



General Information		Optic type	
Lamp family code	TL5 [TL5]	Matt mirror ribbed lamellae louver	
Gear	HFP [HF Performer]	Optical cover type	
Product family code	TPS642 [ARANO]	-	
Embedded control	-	Operating and Electrical	
CE mark	Yes	Input Voltage	230 to 240 V
Flammability mark	For mounting on normally flammable surfaces	Power Consumption	49 W
ENEC mark	ENEC mark	Cable	-
Glow-wire test	Temperature 850 °C, duration 5 s	Mechanical and Housing	
Light Technical		Housing Color	Aluminum
Number of light sources	2	Approval and Application	
Light source color	840 neutral white	Ingress protection code	IP20 [Finger-protected]

Arano TPS640/642/644

Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TPS642 2x49W/840 HFP M2 SMS ALU
Full product name	TPS642 2x49W/840 HFP M2 SMS ALU
Full product code	871155975457400

Order code	910501324303
Material Nr. (12NC)	910501324303
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559754574
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559754574

Dimensional drawing



Product
TPS642 2x49W/840 HFP M2 SMS ALU

