



Arano, asymmetric

TCS649 1x35W/840 HFP A ALU

Arano, 1, 35 W, 840 neutral white, HF Performer, Asymmetrical mirror, Aluminum

Arano asymmetric is a wall-washer luminaire incorporating 1 or 2 TL5 fluorescent lamps. Its best-in-class lighting performance ensures a uniform light distribution, fully compliant with the current norms for office, school and shop lighting. Featuring the Arano family design aesthetic, this luminaire is available in white and aluminum finishes.


Product data

General Information		Mechanical and Housing	
Lamp family code	TL5 [TL5]	Housing Color	Aluminum
Gear	HFP [HF Performer]	Approval and Application	
Product family code	TCS649 [Arano]	Ingress protection code	IP20 [Finger-protected]
CE mark	Yes	Protection class IEC	Safety class I
ENEC mark	ENEC mark	Application Conditions	
Glow-wire test	Temperature 850 °C, duration 5 s	Suitable for random switching	Not applicable
Light Technical		Product Data	
Number of light sources	1	Order product name	TCS649 1x35W/840 HFP A ALU
Light source color	840 neutral white	Full product name	TCS649 1x35W/840 HFP A ALU
Optic type	Asymmetrical mirror	Full product code	871155978790900
Operating and Electrical		Order code	910501349903
Power Consumption	35 W	Material Nr. (12NC)	910501349903
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711559787909

Arano, asymmetric

Numerator - Packs per outer box	1
EAN/UPC - Case	8711559787909

Dimensional drawing



Product	A	B
TCS649 1x35W/840 HFP A ALU	1,494 mm	1,581 mm

