



# Arano, asymmetric

## TCS649 1x80W/840 HFP A ALU

Arano, 1, 80 W, 840 neutral white, HF Performer, Asymmetrical mirror, Aluminum

Arano asymmetric is a wall-washer luminaire incorporating 1 or 2 TL5 fluorescent lamps. Its best-in-class lighting performance ensures a uniform light distribution, fully compliant with the current norms for office, school and shop lighting. Featuring the Arano family design aesthetic, this luminaire is available in white and aluminum finishes.


### Product data

General Information		Mechanical and Housing	
Lamp family code	TL5 [TL5]	Housing Color	Aluminum
Gear	HFP [HF Performer]	<b>Approval and Application</b>	
Product family code	TCS649 [Arano]	Ingress protection code	IP20 [Finger-protected]
CE mark	Yes	Protection class IEC	Safety class I
ENEC mark	ENEC mark	<b>Application Conditions</b>	
Glow-wire test	Temperature 850 °C, duration 5 s	Suitable for random switching	Not applicable
<b>Light Technical</b>		<b>Product Data</b>	
Number of light sources	1	Order product name	TCS649 1x80W/840 HFP A ALU
Light source color	840 neutral white	Full product name	TCS649 1x80W/840 HFP A ALU
Optic type	Asymmetrical mirror	Full product code	871155978796100
<b>Operating and Electrical</b>		Order code	910501350503
Power Consumption	80 W	Material Nr. (12NC)	910501350503
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711559787961

# Arano, asymmetric

Numerator - Packs per outer box	1
EAN/UPC - Case	8711559787961

## Dimensional drawing



Product	A	B
TCS649 1x80W/840 HFP A ALU	1,494 mm	1,581 mm

