



# Arano

## TPS640/642/644

### TPS642 2x80W/840 HFP D8-VH SMS ALU

ARANO, 2, 80 W, 840 neutral white, HF Performer, Semi-high-gloss optic 3D micro-lamellae very high reflectance, Aluminum

Arano is a range of luminaires for TL5 fluorescent lamps and LED light sources, featuring Philips' micro-optics. The patented micro-optic with 3D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully in compliance with the latest office-lighting norm (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

#### Product data



General Information			
Lamp family code	TL5 [TL5]	Optic type	Semi-high-gloss optic 3D micro-lamellae very high reflectance
Gear	HFP [HF Performer]	Optical cover type	-
Product family code	TPS642 [ARANO]	Operating and Electrical	
Embedded control	-	Input Voltage	230 to 240 V
CE mark	Yes	Power Consumption	80 W
Flammability mark	For mounting on normally flammable surfaces	Cable	-
ENEC mark	ENEC mark	Mechanical and Housing	
Glow-wire test	Temperature 850 °C, duration 5 s	Housing Color	Aluminum
Light Technical			
Number of light sources	2		
Light source color	840 neutral white		

Arano TPS640/642/644

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TPS642 2x80W/840 HFP D8-VH SMS ALU
Full product name	TPS642 2x80W/840 HFP D8-VH SMS ALU

Full product code	871155949358900
Order code	910501369403
Material Nr. (12NC)	910501369403
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559493589
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559493589

Dimensional drawing



Product
TPS642 2x80W/840 HFP D8-VH SMS ALU

