



# Arano TCS640

## TCS640 4x24W/840 HFP AC-MLO ALU

ARANO, 4, 24 W, 840 neutral white, HF Performer, Acrylate  
micro-lens optic, Aluminum

Arano is a range of luminaires for TL5 fluorescent lamps and LED light sources, featuring Philips' micro-optics. The patented micro-optic with 3-D lamellae combines a miniaturist design with optimum performance in terms of light distribution, visual comfort and efficiency. And it is fully compliant with the current norm for indoor working places (EN12464-1). Surface-mounted, suspended, free-standing and wall-mounted versions are available – some with direct/indirect lighting – to create a bright, welcoming ambience. Multiple Arano luminaires can be linked to create line arrangements.

## Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFP [HF Performer]
Product family code	TCS640 [ARANO]
Embedded control	-
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
Light Technical	
Number of light sources	4
Light source color	840 neutral white
Optic type	-

Optical cover type	Acrylate micro-lens optic
Operating and Electrical	
Power Consumption	24 W
Cable	-
Mechanical and Housing	
Housing Color	Aluminum
Approval and Application	
Ingress protection code	IP40 [Wire-protected]
Protection class IEC	Safety class I

Arano TCS640

Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TCS640 4x24W/840 HFP AC-MLO ALU
Full product name	TCS640 4x24W/840 HFP AC-MLO ALU
Full product code	871155949371800
Order code	910501370703

Material Nr. (12NC)	910501370703
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559493718
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559493718

Dimensional drawing

