



SmartForm TCS460

TCS460 2x35W/840 HFP H2L C8

SmartForm surface mnt, 2, 35 W, 840 neutral white, HF Performer, High-gloss optic 3D micro-lamellae

We all feel and perform better in a pleasant, comfortable working environment. Designed for use in offices, shops and schools, the SmartForm family of surface-mounted luminaires combines best-in-class lighting with a clean, distinctive design. These ultra-flat luminaires are available with a choice of MASTER TL5, TL5 ECO or LED light sources in rectangular and square versions with direct/indirect lighting combinations. They can also be used to form light-lines and structures. With its wide choice of very efficient and comfortable micro-optics and covers, SmartForm surface-mounted provides the ideal solution for every situation. Lighting controls can be added for further energy saving.

Product data



General Information		Optic type	
Lamp family code	TL5 [TL5]	High-gloss optic 3D micro-lamellae	
Gear	HFP [HF Performer]	Optical cover type	
Feed-through wiring	-	-	
Product family code	TCS460 [SmartForm surface mnt]	Operating and Electrical	
Embedded control	-	Input Voltage	
CE mark	Yes	220 to 240 V	
Flammability mark	For mounting on normally flammable surfaces	Power Consumption	
ENEC mark	ENEC mark	35 W	
Glow-wire test	Temperature 960 °C, duration 5 s	Connection	
Light Technical		Push-in connector 3-pole	
Number of light sources	2	Cable	
Light source color	840 neutral white	-	
		Mechanical and Housing	
		Fixation point length distance (Nom)	
		1,355 mm	
		Housing Color	
		White	
		Overall length	
		1,540 mm	

SmartForm TCS460

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TCS460 2x35W/840 HFP H2L C8

Full product name	TCS460 2x35W/840 HFP H2L C8
Full product code	871794399199000
Order code	910501392803
Material Nr. (12NC)	910501392803
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943991990
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943991990

Dimensional drawing



Product	A	B
TCS460 2x35W/840 HFP H2L C8	1,355 mm	1,540 mm

