



# SmartForm TPS460/462/464

## TPS460 2x35W/840 HFP H2L MLO-PC SMT1

SmartForm suspended, 2, 35 W, 77 W, 840 neutral white, HF Performer, Micro-lens optic in polycarbonate cover

We all feel and perform better in a pleasant, comfortable working environment. Designed for use in offices, shops and schools, the SmartForm family of suspended mounted luminaires combines best-in-class lighting with a clean, distinctive design. These ultra-flat luminaires are available with a choice of MASTER TL5, TL5 ECO or LED light sources in rectangular and square versions with direct/indirect lighting combinations. They can also be used to form light-lines and structures. With its wide choice of very efficient and comfortable micro-optics and covers, SmartForm suspended provides the ideal solution for every situation. Lighting controls can be added for further energy saving.

### Product data

General Information			
Lamp family code	TL5 [TL5]	Flammability mark	For mounting on normally flammable surfaces
Cap-Base	G5 [G5]	ENEC mark	ENEC mark
Light source replaceable	Yes	Glow-wire test	Temperature 850 °C, duration 5 s
Number of gear units	1 unit	EU RoHS compliant	Yes
Gear	HFP [HF Performer]	Light Technical	
Driver included	Yes	Luminous Flux	3,990 lm
Product family code	TPS460 [SmartForm suspended]	Correlated Color Temperature (Nom)	4000 K
Embedded control	-	Luminous Efficacy (rated) (Nom)	52 lm/W
CE mark	Yes	Color rendering index (CRI)	82
Warranty period	5 years	Number of light sources	2

SmartForm TPS460/462/464

Light source color	840 neutral white
Optic type	-
Optical cover type	Micro-lens optic in polycarbonate cover
Luminaire light beam spread	130°

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	48 A
Inrush time	1 ms
Power Consumption	35 77 W
Power Factor (Fraction)	0.96
Connection	Push-in connector 3-pole
Cable	Cable with CEE 7 plug 3-pole
Number of products on MCB of 16 A type B -	

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------


Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Electronic transformer
Constant light output	No

Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	-
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	White
Optical cover finish	Textured
Overall length	1,540 mm
Overall width	217 mm

Dimensional drawing



Product	A	B
TPS460 2x35W/840 HFP H2L MLO-PC SMT1	1,486 mm	1,540 mm

Overall height	49 mm
Dimensions (Height x Width x Depth)	49 x 217 x 1540 mm

Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1 %
-------------------------------	-----

Application Conditions

Suitable for random switching	No
-------------------------------	----

Product Data

Order product name	TPS460 2x35W/840 HFP H2L MLO-PC SMT1
Full product name	TPS460 2x35W/840 HFP H2L MLO-PC SMT1
Full product code	871794399203400
Order code	910501393203
Material Nr. (12NC)	910501393203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943992034
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943992034

