

TBH375

TBH375 2xTL-D58W/830 HFP PI

TBH375, 2, MASTER TL-D, 58 W, 830 warm white, HF Performer, Push-in connector 3-pole

Ball-impact-resistant luminaire for TL-D fluorescent lamps, specially designed for multipurpose sports halls and tennis halls. Lamellae prevent players from seeing directly into the lamps. Strong housing construction protects lamps against ball impact. For surface or recessed mounting. Optics supplied with the luminaire.


Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFP [HF Performer]
Product family code	TBH375 [TBH375]
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Number of light sources	2
Light source color	830 warm white
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	58 W
Connection	Push-in connector 3-pole
Mechanical and Housing	
Overall width	313 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TBH375 2xTL-D58W/830 HFP PI
Full product name	TBH375 2xTL-D58W/830 HFP PI
Full product code	871155975804600
Order code	910501733803
Material Nr. (12NC)	910501733803
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559758046
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559758046

TBH375

Dimensional drawing



Product
TBH375 2xTL-D58W/830 HFP PI

