



TBH375

TBH375 2xTL5-80W/830 HFP PI

TBH375, 2, TL5, 80 W, 830 teplá bílá, HF Performer, Zasunovací konektor třípólový


Ball-impact-resistant luminaire for TL-D fluorescent lamps, specially designed for multipurpose sports halls and tennis halls. Lamellae prevent players from seeing directly into the lamps. Strong housing construction protects lamps against ball impact. For surface or recessed mounting. Optics supplied with the luminaire.

Údaje o produktu

| Obecné informace | | Certifikace a použití | |
|-------------------------|-------------------------------|----------------------------------|--------------------------------------|
| Kód řady svítidel | TL5 [TL5] | Kód ochrany proti vniknutí | IP20 [Chráněno proti vniknutí prstů] |
| Předřadník | HFP [HF Performer] | Třída ochrany IEC | Bezpečnostní třída I |
| Kód produktové řady | TBH375 [TBH375] | | |
| Značka CE | Ano | | |
| Značka ENEC | Značka ENEC | | |
| Světelně technické | | Podmínky použití | |
| Počet světelných zdrojů | 2 | Vhodné pro náhodné spínání | Nevztahuje se |
| Barva světelného zdroje | 830 teplá bílá | | |
| Provozní a elektrické | | Označení a balení | |
| Vstupní napětí | 220 až 240 V | Objednávací název produktu | TBH375 2xTL5-80W/830 HFP PI |
| Spotřeba energie | 80 W | Celý název výrobku | TBH375 2xTL5-80W/830 HFP PI |
| Připojení | Zasunovací konektor třípólový | Full EOC | 871155975808400 |
| | | Objednávací kód | 75808400 |
| Mechanické a materiály | | Číslo materiálu (12NC) | 910501734003 |
| Celková šířka | 313 mm | Číslování SAP – počet v balení | 1 |
| | | EAN/UPC – výrobek/pouzdro | 8711559758084 |
| | | Číslování SAP – balení v krabici | 1 |
| | | Pouzdro – EAN/UPC | 8711559758084 |

TBH375

Rozměrové výkresy



Product

TBH375 2xTL5-80W/830 HFP PI

