

# SmartForm TBS460

## TBS460 2x28W/840 HFP D8-VH PIP IP

SmartForm recessed modular, 2, 28 W, 840 neutral white, HF Performer, Semi-high-gloss optic 3D micro-lamellae very high reflectance, Push-in connector and pull relief

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in square and rectangular versions. Designed to fit in a wide range of ceiling types, SmartForm can fulfill the majority of project requirements in most applications. Energy efficiency. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m<sup>2</sup> is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO<sub>2</sub> levels, making SmartForm an environmentally friendly choice. SmartForm recessed TBS460 – ultra-flat 'light beam'. SmartForm recessed TBS460 'light beam' luminaires are built around superior micro-optics and have a build-in height of a mere 45 mm, making them ideal for applications requiring very flat light fittings, e.g. refurbishment projects where ceiling space may be especially limited.

### Product data


General Information		Flammability mark	
Lamp family code	TL5 [TL5]	ENEC mark	For mounting on normally flammable surfaces
Gear	HFP [HF Performer]	Glow-wire test	ENEC mark
Product family code	TBS460 [SmartForm recessed modular]		Temperature 850 °C, duration 5 s
Embedded control	-	Light Technical	
CE mark	Yes	Number of light sources	2

SmartForm TBS460

Light source color	840 neutral white
Optic type	Semi-high-gloss optic 3D micro-lamellae very high reflectance
Optical cover type	-
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	28 W
Connection	Push-in connector and pull relief
Cable	-
Mechanical and Housing	
Housing Color	White
Overall length	1,197 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TBS460 2x28W/840 HFP D8-VH PIP IP
Full product name	TBS460 2x28W/840 HFP D8-VH PIP IP
Full product code	871150000385000
Order code	00385000
Material Nr. (12NC)	910501786103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500003850
Numerator - Packs per outer box	1
EAN/UPC - Case	8711500003850

Dimensional drawing



Product	A
TBS460 2x28W/840 HFP D8-VH PIP IP	1,197 mm

