

SmartForm TBS460

TBS460 2x54W/840 HFP C8 FU W4 IP

SmartForm recessed modular, 2, 54 W, 840 neutral white, HF Performer, High-gloss optic 3D micro-lamellae, Fuse included, Plug-in connector 4-pole Wieland/Adels compatible

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in square and rectangular versions. Designed to fit in a wide range of ceiling types, SmartForm can fulfill the majority of project requirements in most applications. Energy efficiency. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m² is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO₂ levels, making SmartForm an environmentally friendly choice. SmartForm recessed TBS460 – ultra-flat 'light beam'. SmartForm recessed TBS460 'light beam' luminaires are built around superior micro-optics and have a build-in height of a mere 45 mm, making them ideal for applications requiring very flat light fittings, e.g. refurbishment projects where ceiling space may be especially limited.

Product data

General Information			
Lamp family code	TL5 [TL5]	Flammability mark	For mounting on normally flammable surfaces
Gear	HFP [HF Performer]	ENEC mark	ENEC mark
Product family code	TBS460 [SmartForm recessed modular]	Glow-wire test	Temperature 850 °C, duration 5 s
Embedded control	-	Light Technical	
CE mark	Yes	Number of light sources	2

SmartForm TBS460

Light source color	840 neutral white
Optic type	High-gloss optic 3D micro-lamellae
Optical cover type	-

Operating and Electrical

Input Voltage	220 to 240 V
Power Consumption	54 W
Connection	Plug-in connector 4-pole Wieland/Adels compatible
Cable	-

Mechanical and Housing

Housing Color	White
Overall length	1,197 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Protection class IEC	Safety class I
----------------------	----------------


Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------

Product Data

Order product name	TBS460 2x54W/840 HFP C8 FU W4 IP
Full product name	TBS460 2x54W/840 HFP C8 FU W4 IP
Full product code	871150000424600
Order code	910501790003
Material Nr. (12NC)	910501790003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500004246
Numerator - Packs per outer box	1
EAN/UPC - Case	8711500004246

Dimensional drawing



Product	A
TBS460 2x54W/840 HFP C8 FU W4 IP	1,197 mm

