

# SmartForm TBS417

## TBS417 1x35W/840 HFP C8 PIP

SmartForm recessed semi-modular, 1, 35 W, 840 neutral white, HF Performer, High-gloss optic 3D micro-lamellae, Push-in connector and pull relief

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption ( $W/m^2$  is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO<sub>2</sub> levels, making SmartForm an environmentally friendly choice. Slender SmartForm recessed continuous light-line luminaires are designed for integration in linear exposed T-bar and plaster ceilings. Continuous light line for micro-optics, asymmetrical optic and rimless MLO and Opal covers. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 90 mm. Continuous light line for mini-optics, 2-lamps. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 115 mm.

### Product data

General Information		Embedded control	
Lamp family code	TL5 [TL5]		-
Gear	HFP [HF Performer]	CE mark	Yes
Feed-through wiring	-	Glow-wire test	Temperature 850 °C, duration 5 s
Product family code	TBS417 [SmartForm recessed semi-modular]		

# SmartForm TBS417

## Light Technical

Number of light sources	1
Light source color	840 neutral white
Optic type	High-gloss optic 3D micro-lamellae
Optical cover type	-

## Operating and Electrical

Input Voltage	220 to 240 V
Power Consumption	35 W
Connection	Push-in connector and pull relief
Cable	-

## Mechanical and Housing

Housing Color	White
Overall length	1,508 mm

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	-------------------------

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I



## Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------

## Product Data

Order product name	TBS417 1x35W/840 HFP C8 PIP
Full product name	TBS417 1x35W/840 HFP C8 PIP
Full product code	871794398772600
Order code	910501898403
Material Nr. (12NC)	910501898403
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943987726
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943987726

## Dimensional drawing



Product	A
TBS417 1x35W/840 HFP C8 PIP	1,508 mm

