

SmartForm TBS417

TBS417 1x28W/840 HFP D8-VH W

SmartForm recessed semi-modular, 1, 28 W, 840 neutral white, HF Performer, Semi-high-gloss optic 3D micro-lamellae very high reflectance, Plug-in connector 3-pole Wieland/Adels compatible

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m^2 is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO₂ levels, making SmartForm an environmentally friendly choice. Slender SmartForm recessed continuous light-line luminaires are designed for integration in linear exposed T-bar and plaster ceilings. Continuous light line for micro-optics, asymmetrical optic and rimless MLO and Opal covers. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 90 mm. Continuous light line for mini-optics, 2-lamps. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 115 mm.

Product data


General Information		Product family code	
Lamp family code	TL5 [TL5]	Product family code	TBS417 [SmartForm recessed semi-modular]
Gear	HFP [HF Performer]	Embedded control	-
Feed-through wiring	-	CE mark	Yes

SmartForm TBS417

Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	1
Light source color	840 neutral white
Optic type	Semi-high-gloss optic 3D micro-lamellae very high reflectance
Optical cover type	-
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	28 W
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-
Mechanical and Housing	
Housing Color	White
Overall length	1,208 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TBS417 1x28W/840 HFP D8-VH W
Full product name	TBS417 1x28W/840 HFP D8-VH W
Full product code	871794398796200
Order code	910501900803
Material Nr. (12NC)	910501900803
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943987962
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943987962

Dimensional drawing



Product	A
TBS417 1x28W/840 HFP D8-VH W	1,208 mm

