

# SmartForm TBS417

## TBS417 1x49W/830 HFP D8 W

SmartForm recessed semi-modular, 1, 49 W, 830 warm white, HF Performer, Semi-high-gloss optic 3D micro-lamellae, Plug-in connector 3-pole Wieland/Adels compatible

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m<sup>2</sup> is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO<sub>2</sub> levels, making SmartForm an environmentally friendly choice. Slender SmartForm recessed continuous light-line luminaires are designed for integration in linear exposed T-bar and plaster ceilings. Continuous light line for micro-optics, asymmetrical optic and rimless MLO and Opal covers. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 90 mm. Continuous light line for mini-optics, 2-lamps. All versions TL5: 14/24 W; 21/39 W; 28/54 W; 35/49/80 W. Luminaire width is 115 mm.

### Product data



General Information		Product family code	TBS417 [SmartForm recessed semi-modular]
Lamp family code	TL5 [TL5]	Lighting Technology	Fluorescent
Cap-Base	G5 [G5]	Embedded control	-
Gear	HFP [HF Performer]	CE mark	Yes
Feed-through wiring	-	Flammability mark	For mounting on normally flammable surfaces

SmartForm TBS417

ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Luminous Flux	4,900 lm
Luminous Efficacy (rated) (Nom)	100 lm/W
Number of light sources	1
Light source color	830 warm white
Optic type	Semi-high-gloss optic 3D micro-lamellae
Optical cover type	-
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	49 W
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-
Temperature	
Ambient temperature range	+10 to +40 °C
Mechanical and Housing	
Housing Material	Steel
Reflector material	Aluminum
Optic material	Aluminum
Fixation material	-
Housing Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	1%
Suitable for random switching	No
Product Data	
Order product name	TBS417 1x49W/830 HFP D8 W
Full product name	TBS417 1x49W/830 HFP D8 W
Full product code	871794398926300
Order code	910501913803
Material Nr. (12NC)	910501913803
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943989263
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943989263

Dimensional drawing



Product	A
TBS417 1x49W/830 HFP D8 W	1,508 mm

