

SmartForm TBS411

TBS411 1x28W/830 HFP C8 W SC

SmartForm recessed semi-modular, 1, 28 W, 830 warm white, HF Performer, High-gloss optic 3D micro-lamellae, Plug-in connector 3-pole Wieland/Adels compatible

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m² is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO₂ levels, making SmartForm an environmentally friendly choice. These slender SmartForm recessed luminaires are designed for integration in variety of linear ceiling systems: exposed and concealed T-bar, plaster and the extended versions for bandraster ceilings. Micro-optics and covers (MLO-PC and Opal) in smallest concept, width 90 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm. Micro-optics and covers in smallest concept with AIR function, width 100 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm. Mini-optics, 2-lamps, width 115 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm.

Product data

General Information			
Lamp family code	TL5 [TL5]	Feed-through wiring	-
Gear	HFP [HF Performer]	Product family code	TBS411 [SmartForm recessed semi-modular]
		Embedded control	-

SmartForm TBS411

CE mark	Yes
Warranty period	5 years
Glow-wire test	Temperature 850 °C, duration 5 s

Light Technical

Number of light sources	1
Light source color	830 warm white
Optic type	High-gloss optic 3D micro-lamellae
Optical cover type	-

Operating and Electrical

Input Voltage	220 to 240 V
Power Consumption	28 W
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-

Mechanical and Housing

Housing Color	White
Overall length	1,197 mm
Overall width	90 mm
Overall height	98 mm

Dimensions (Height x Width x Depth)	98 x 90 x 1197 mm
-------------------------------------	-------------------

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I



Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------

Product Data

Order product name	TBS411 1x28W/830 HFP C8 W SC
Full product name	TBS411 1x28W/830 HFP C8 W SC
Full product code	871794399048100
Order code	910501926003
Material Nr. (12NC)	910501926003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943990481
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943990481

Dimensional drawing



Product	A
TBS411 1x28W/830 HFP C8 W SC	1,197 mm

