



# CoreLine surface-mounted

## SM120V LED27S/830 PSD W60L60

Coreline Surface, LED Module, system flux 2700 lm, 830 warm white, Power supply unit with DALI interface

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Surface-mounted range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

### Product data

General Information		
Lamp family code	LED27S [LED Module, system flux 2700 lm]	is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	
Light source replaceable	No	
Number of gear units	1 unit	
Gear	-	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper “Evaluating performance of LED based luminaires – January 2018”: statistically there	

Product family code	SM120V [Coreline Surface]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	3 years + 2 years upon registration
Flammability mark	For mounting on normally flammable surfaces

## CoreLine surface-mounted

ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 30 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	2,700 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	102 lm/W
Color rendering index (CRI)	≥80
Number of light sources	2
Light source color	830 warm white
Optic type	Wide beam
Optical cover type	Polycarbonate linear satinized
Luminaire light beam spread	86°
Unified glare rating CEN	Not applicable

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	14.7 A
Inrush time	0.25 ms
Power Consumption	30.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	38

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Steel
------------------	-------

Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Textured
Overall length	597 mm
Overall width	597 mm
Overall height	36 mm
Dimensions (Height x Width x Depth)	36 x 597 x 597 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

### Product Data

Order product name	SM120V LED27S/830 PSD W60L60
Full product name	SM120V LED27S/830 PSD W60L60
Full product code	871829126831400
Order code	26831400
Material Nr. (12NC)	910501990603
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291268314
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291268314

## CoreLine surface-mounted

### Dimensional drawing

