



CoreLine recessed

RC120B LED27S/830 PSD W60L60 VAR-PC

Coreline Recessed, LED Module, system flux 2700 lm, 830 warm white, Power supply unit with DALI interface, Variable linear-lens array in polycarbonate cover

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Recessed range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch. In addition, Coreline Recessed also provides the option of advanced connectivity and is ready to be connected to IoT based software applications such as Interact Pro.

Warnings and Safety

- The product is IPX0 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void

Product data

General Information			
Lamp family code	LED27S [LED Module, system flux 2700 lm]	luminaires – January 2018*: statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Cap base	- [-]		
Light source replaceable	No		
Number of gear units	Unit		
Gear	EB [Electronic]		
Driver included	Yes	Product family code	RC120B [Coreline Recessed]
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based	Lighting Technology	LED
		Value ladder	Performance

CoreLine recessed

CE mark	Yes
Warranty period	3 years + 2 years upon registration
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 30 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	2,700 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	115 lm/W
Colour rendering index (CRI)	≥80
Light source colour	830 warm white
Optic type	Wide beam
Optical cover type	Variable linear-lens array in polycarbonate cover
Luminaire light beam spread	75°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	14.7 A
Inrush time	0.25 ms
Power Consumption	23.1 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	38

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Steel
Reflector material	Steel

Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Textured
Overall length	597 mm
Overall width	597 mm
Overall height	32 mm
Dimensions (height x width x depth)	32 x 597 x 597 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L75

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	RC120B LED27S/830 PSD W60L60 VAR-PC
Full product name	RC120B LED27S/830 PSD W60L60 VAR-PC
Full EOC	871829126657000
Order code	26657000
Material no. (12 NC)	910501997003
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291266570
Numerator – packs per outer box	1
EAN/UPC - Case	8718291266570

CoreLine recessed

Dimensional drawing

