



PowerBalance gen2

RC461B G2 LED34S/840 PSD W30L120 VPC W

PowerBalance recessed, Generation 2, LED module, system flux 3400 lm, 840 neutral white, Power supply unit with DALI interface, Plug-in connector 3-pole Wieland/Adels compatible

When it comes to lighting an office space with LED luminaires, people are usually willing to invest in sustainability provided the investment pays back. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. PowerBalance gen2 is Philips' most energy-efficient office-norm-compliant LED luminaire. It more than halves energy costs compared to a T5 solution, and the light source has a longer lifetime. This results in significantly lower operational costs, ensuring a payback that meets the needs of the specification market. The gen2 architecture enables a range of highly versatile modular and semi-modular luminaires. These luminaires can be easily mounted in ceilings with exposed T-bar and concealed T-bar, as well as plaster ceiling types.

Warnings and Safety

- The product is IP20 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe use and the product warranty will become void

Product data

General Information		Remarks
Lamp family code	LED34S [LED module, system flux 3400 lm]	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median
Cap base	- [-]	
Light source replaceable	No	
Number of gear units	Unit	
Driver included	Yes	

PowerBalance gen2

	useful life (B50) value also represents the B10 value.
Product family code	RC461B [PowerBalance recessed]
Lighting Technology	LED
Value ladder	Specification
Embedded control	-
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC plus mark
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	3,400 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	136 lm/W
Colour rendering index (CRI)	≥80
Light source colour	840 neutral white
Optic type	-
Luminaire light beam spread	86°
Unified Glare Rating (CEN)	16

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	5 A
Inrush time	1 ms
Power Consumption	25 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Steel
------------------	-------

Reflector material	Polycarbonate
Optic material	-
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White RAL 9003
Optical cover/lens finish	Matte
Overall length	1,197 mm
Overall width	297 mm
Overall height	79 mm
Dimensions (height x width x depth)	79 x 297 x 1197 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L90

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

Product Data

Order product name	RC461B G2 LED34S/840 PSD W30L120 VPC W
Full product name	RC461B G2 LED34S/840 PSD W30L120 VPC W
Full EOC	871829126802400
Order code	26802400
Material no. (12 NC)	910502007903
Local order code	8717943102709
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291268024
Numerator – packs per outer box	1
EAN/UPC – Case	8718291268024

PowerBalance gen2

Dimensional drawing

