



# ArcForm

## RC660B LED44S/840 PSD W60L60 MO-PC W

ArcForm, LED Module, system flux 4400 lm, 840 neutral white, Power supply unit with DALI interface, MESO optic in polycarbonate cover, Plug-in connector 3-pole Wieland/Adels compatible and 2-pole control signal for light regulation

More and more customers are looking for lighting solutions that support the architecture of the building and the types of activity taking place in certain zones. A luminaire with soft light and a gentle appearance is perfect for those places where additional quality of light adds value. With the cleanly designed ArcForm, the optical system using MesoOptics technology creates soft, comfortable lighting, with a full luminous surface. The luminaire's wide beam shape means that the light distribution is uniform throughout the entire space, rather than directional. And the LED boards and optics offer significant energy savings compared to a similar conventional solution.

### Product data

General Information			
Lamp family code	LED44S [LED Module, system flux 4400 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	Product family code	RC660B [ArcForm]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	1 unit	Glow-wire test	Temperature 850 °C, duration 5 s
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	CE mark	Yes
		ENEC mark	ENEC mark
		Warranty period	5 years
		EU RoHS compliant	Yes

<b>Light Technical</b>	
Luminous Flux	4,400 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	122 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Light source color	840 neutral white
Optic type	-
Optical cover type	MESO optic in polycarbonate cover
Luminaire light beam spread	120°
Unified glare rating CEN	Not applicable
<b>Operating and Electrical</b>	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	5 A
Inrush time	1 ms
Power Consumption	36 W
Power Factor (Fraction)	0.93
Connection	Plug-in connector 3-pole Wieland/Adels compatible and 2-pole control signal for light regulation
Cable	-
Number of products on MCB of 16 A type B	20
<b>Temperature</b>	
Ambient temperature range	+10 to +40 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
<b>Mechanical and Housing</b>	
Housing Material	Steel
Reflector material	Aluminum
Optic material	-
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White

Optical cover finish	Clear
Overall length	597 mm
Overall width	597 mm
Overall height	161 mm
Dimensions (Height x Width x Depth)	161 x 597 x 597 mm
<b>Approval and Application</b>	
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%
<b>Over Time Performance (IEC Compliant)</b>	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80
<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No
<b>Product Data</b>	
Order product name	RC660B LED44S/840 PSD W60L60 MO-PC W
Full product name	RC660B LED44S/840 PSD W60L60 MO-PC W
Full product code	871829127382000
Order code	910502014703
Material Nr. (12NC)	910502014703
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291273820
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291273820

Dimensional drawing

