



CitySoul

CGP430 CPO-T60W/728 EB II FG GR 60S

CITY SOUL MINI, MASTER CosmoWhite CPO-TW, 60 W,
Electronic, Optic for CosmoPolis lamp, Flat glass, Side-entry for
diameter 60 mm

CitySoul is a family of modular street-lighting luminaires featuring state-of-the-art lamp and gear technologies – including LED – and offering outstanding optical performance. Its classic design merges well with today's urban environment. The simple, flat, ellipsoidal form of the luminaire creates an elegant light-point. Suitable for side-entry, suspended or post-top installation, and with its adjustable beam and light trespass accessories, this versatile luminaire fits every application. CitySoul comes in two sizes, along with a complete range of dedicated masts and brackets.


Product data

General Information		Operating and Electrical	
Lamp family code	CPO-TW [MASTER CosmoWhite CPO-TW]	Input Voltage	220 to 240 V
Gear	EB [Electronic]	Power Consumption	60 W
Photocell	-	Connection	-
Product family code	CGP430 [CITY SOUL MINI]	Mechanical and Housing	
Embedded control	-	Housing Color	Grey
CE mark	Yes	Mounting device	Side-entry for diameter 60 mm
ENEC mark	ENEC mark	Overall length	749 mm
Light Technical		Overall width	400 mm
Number of light sources	1	Overall height	197 mm
Light source color	728 warm white	Dimensions (Height x Width x Depth)	197 x 400 x 749 mm
Optical cover type	Flat glass	Approval and Application	
Optic type outdoor	Optic for CosmoPolis lamp	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK09 [10 J]
Protection class IEC	Safety class II
Product Data	
Full product code	871155967956300
Order product name	CGP430 CPO-T60W/728 EB II FG GR 60S
Order code	910502119918
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	1
Material Nr. (12NC)	910502119918
Full product name	CGP430 CPO-T60W/728 EB II FG GR 60S
EAN/UPC - Case	8711559679563
EAN/UPC - Product/Case	8711559679563

Dimensional drawing



Product	A	B	C	D
CGP430 CPO-T60W/728 EB II FG GR 60S	171 mm	510 mm	749 mm	400 mm

