



# CitySoul

## CGP430 CPO-T60W/728 EB II FG GR 76P

CITY SOUL MINI, MASTER CosmoWhite CPO-TW, 60 W,  
Electronic, Optic for CosmoPolis lamp, Flat glass, Post-top for  
diameter 76 mm

CitySoul is a family of modular street-lighting luminaires featuring state-of-the-art lamp and gear technologies – including LED – and offering outstanding optical performance. Its classic design merges well with today's urban environment. The simple, flat, ellipsoidal form of the luminaire creates an elegant light-point. Suitable for side-entry, suspended or post-top installation, and with its adjustable beam and light trespass accessories, this versatile luminaire fits every application. CitySoul comes in two sizes, along with a complete range of dedicated masts and brackets.


### Product data

General Information		Operating and Electrical	
Lamp family code	CPO-TW [MASTER CosmoWhite CPO-TW]	Input Voltage	220 to 240 V
Gear	EB [Electronic]	Power Consumption	60 W
Photocell	-	Mechanical and Housing	
Product family code	CGP430 [CITY SOUL MINI]	Housing Color	Grey
Embedded control	-	Mounting device	Post-top for diameter 76 mm
CE mark	Yes	Overall length	644 mm
ENEC mark	ENEC mark	Overall width	400 mm
Light Technical		Approval and Application	
Number of light sources	1	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Light source color	728 warm white	Mech. impact protection code	IK09 [10 J]
Optical cover type	Flat glass	Protection class IEC	Safety class II
Optic type outdoor	Optic for CosmoPolis lamp		

Product Data	
Full product code	871155947909500
Order product name	CGP430 CPO-T60W/728 EB II FG GR 76P
Order code	910502208318
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Material Nr. (12NC)	910502208318
Full product name	CGP430 CPO-T60W/728 EB II FG GR 76P
EAN/UPC - Case	8711559479095
EAN/UPC - Product/Case	8711559479095

Dimensional drawing



Product	A	B	C	D
CGP430 CPO-T60W/728 EB II FG GR 76P	171 mm	510 mm	644 mm	400 mm

