



# CitySoul

## CGP430 SON-T100W K II FG GR SND 76P

CITY SOUL MINI, SON-T, 100 W, Flat glass, Post-top for diameter 76 mm

CitySoul is a family of modular street-lighting luminaires featuring state-of-the-art lamp and gear technologies – including LED – and offering outstanding optical performance. Its classic design merges well with today’s urban environment. The simple, flat, ellipsoidal form of the luminaire creates an elegant light-point. Suitable for side-entry, suspended or post-top installation, and with its adjustable beam and light trespass accessories, this versatile luminaire fits every application. CitySoul comes in two sizes, along with a complete range of dedicated masts and brackets.


### Product data

|                                 |                         |  |  |
|---------------------------------|-------------------------|--|--|
| <b>General Information</b>      |                         | <b>Power Consumption</b>                     |  |
| Lamp family code                | SON-T [SON-T]           | 100 W  |  |
| Gear                            | CONV [Conventional]     | <b>Mechanical and Housing</b>                |  |
| Photocell                       | -                       | Housing Color                                |  |
| Product family code             | CGP430 [CITY SOUL MINI] | Grey   |  |
| Embedded control                | -                       | Mounting device                              |  |
| CE mark                         | Yes                     | Post-top for diameter 76 mm                  |  |
| ENEC mark                       | ENEC mark               | Overall length                               |  |
| <b>Light Technical</b>          |                         | 644 mm                                       |  |
| Number of light sources         | 1                       | Overall width                                |  |
| Optical cover type              | Flat glass              | 400 mm                                       |  |
| <b>Operating and Electrical</b> |                         | <b>Approval and Application</b>              |  |
| Input Voltage                   | 230 V                   | Ingress protection code                      |  |
|                                 |                         | IP66 [Dust penetration-protected, jet-proof] |  |
|                                 |                         | Mech. impact protection code                 |  |
|                                 |                         | IK09 [10 J]                                  |  |
|                                 |                         | Protection class IEC                         |  |
|                                 |                         | Safety class II                              |  |
|                                 |                         | <b>Product Data</b>                          |  |
|                                 |                         | Full product code                            |  |
|                                 |                         | 871155947911800                              |  |
|                                 |                         | Order product name                           |  |
|                                 |                         | CGP430 SON-T100W K II FG GR SND 76P          |  |

|                                 |                                     |
|---------------------------------|-------------------------------------|
| Order code                      | 910502208518                        |
| Numerator - Quantity Per Pack   | 1                                   |
| Numerator - Packs per outer box | 1                                   |
| Material Nr. (12NC)             | 910502208518                        |
| Full product name               | CGP430 SON-T100W K II FG GR SND 76P |

|                        |               |
|------------------------|---------------|
| EAN/UPC - Case         | 8711559479118 |
| EAN/UPC - Product/Case | 8711559479118 |

Dimensional drawing



| Product                             | A      | B      | C      | D      |
|-------------------------------------|--------|--------|--------|--------|
| CGP430 SON-T100W K II FG GR SND 76P | 171 mm | 510 mm | 644 mm | 400 mm |

