



CitySoul

CGP430 CPO-T90W/728 EB II FG GR 60S

CITY SOUL MINI, MASTER CosmoWhite CPO-TW, 90 W,
Electronic, Flat glass, Side-entry for diameter 60 mm

CitySoul is a family of modular street-lighting luminaires featuring state-of-the-art lamp and gear technologies – including LED – and offering outstanding optical performance. Its classic design merges well with today’s urban environment. The simple, flat, ellipsoidal form of the luminaire creates an elegant light-point. Suitable for side-entry, suspended or post-top installation, and with its adjustable beam and light trespass accessories, this versatile luminaire fits every application. CitySoul comes in two sizes, along with a complete range of dedicated masts and brackets.

Product data


General Information	
Lamp family code	CPO-TW [MASTER CosmoWhite CPO-TW]
Gear	EB [Electronic]
Photocell	-
Product family code	CGP430 [CITY SOUL MINI]
Embedded control	-
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Number of light sources	1
Light source color	728 warm white
Optical cover type	Flat glass
Operating and Electrical	
Input Voltage	220 to 240 V

Power Consumption	90 W
Mechanical and Housing	
Housing Color	Grey
Mounting device	Side-entry for diameter 60 mm
Overall length	749 mm
Overall width	400 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Protection class IEC	Safety class II
Product Data	
Full product code	872790060273900
Order product name	CGP430 CPO-T90W/728 EB II FG GR 60S

Order code	910502270018
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910502270018
Full product name	CGP430 CPO-T90W/728 EB II FG GR 60S

EAN/UPC - Case	8727900602739
EAN/UPC - Product/Case	8727900602739

Dimensional drawing



Product	A	B	C	D
CGP430 CPO-T90W/728 EB II FG GR 60S	171 mm	510 mm	749 mm	400 mm

