



Zadora, adjustable

QBD570 1xHAL-FR50-50W K ET ALU

ZADORA, 1, 50 W, Aluminum

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

Product data

General Information	
Cap-Base	E27 [E27]
Gear	-
Product family code	QBD570 [ZADORA]
Lighting Technology	LED
Value ladder	Value
Light Technical	
Number of light sources	1
Luminaire light beam spread	108°
Operating and Electrical	
Input Voltage	12 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	50 W
Connection	-

Temperature	
Ambient temperature range	-10 to +35 °C
Controls and Dimming	
Driver/power unit/transformer	Electronic transformer
Mechanical and Housing	
Housing Color	Aluminum
Overall length	75 mm
Overall width	322 mm
Overall height	322 mm
Dimensions (Height x Width x Depth)	322 x 322 x 75 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK00 [No protection]
Protection class IEC	Safety class II
Product Data	
Order product name	QBD570 1xHAL-FR50-50W K ET ALU

Zadora, adjustable

Full product name	QBD570 1xHAL-FR50-50W K ET ALU
Full product code	871155957435600
Order code	910502532718
Material Nr. (12NC)	910502532718
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8711559574356
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559574356

Dimensional drawing

