



Pentura Mini

TCH128 1xTL5-14W/830 HF

1, TL5, 14 W, 830 warm white, Electronic high-frequency

Pentura Mini TCH128 is an ultra-slim decorative batten for domestic applications. A cost-effective, ready-to-install mini fluorescent solution. Pentura Mini TCH128 offers the energy-saving benefits of miniature fluorescent lamp technology coupled with lightweight electronics and a patented internal reflector for improved lighting performance. The batten is easy to install e.g. over worktops and workstations in the home, home office and recreational environments, etc. it provides bright light where needed even where installation space is limited. Pentura Mini TCH128 battens are fitted with lamp, tough polycarbonate diffuser and all fixing accessories, reducing installation time to a minimum. The battens are through-wired with removeable end-caps at both ends covering the push-button connection blocks for simple connection and through-wiring.

Product data


General Information		Power Consumption	
Lamp family code	TL5 [TL5]	14 W	
Gear	HF [Electronic high-frequency]	Approval and Application	
CE mark	Yes	Ingress protection code	IP20 [Finger-protected]
Flammability mark	For mounting on normally flammable surfaces	Protection class IEC	Safety class II
Glow-wire test	Temperature 850 °C, duration 5 s	Application Conditions	
Light Technical		Suitable for random switching	Not applicable
Number of light sources	1	Product Data	
Light source color	830 warm white	Order product name	TCH128 1xTL5-14W/830 HF
Operating and Electrical		Full product name	TCH128 1xTL5-14W/830 HF
Input Voltage	220 to 240 V	Full product code	871155914852699
		Order code	910502537418

Pentura Mini

Material Nr. (12NC)	910502537418
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559148526
Numerator - Packs per outer box	16

EAN/UPC - Case	8711559804521
----------------	---------------

Dimensional drawing



Product	A
TCH128 1xTL5-14W/830 HF	623 mm

