



# Pentura Mini

## TCH128 1xTL5-21W/840 HF

1, TL5, 21 W, 840 neutral white, Electronic high-frequency

Pentura Mini TCH128 is an ultra-slim decorative batten for domestic applications. A cost-effective, ready-to-install mini fluorescent solution. Pentura Mini TCH128 offers the energy-saving benefits of miniature fluorescent lamp technology coupled with lightweight electronics and a patented internal reflector for improved lighting performance. The batten is easy to install e.g. over worktops and workstations in the home, home office and recreational environments, etc. it provides bright light where needed even where installation space is limited. Pentura Mini TCH128 battens are fitted with lamp, tough polycarbonate diffuser and all fixing accessories, reducing installation time to a minimum. The battens are through-wired with removeable end-caps at both ends covering the push-button connection blocks for simple connection and through-wiring.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HF [Electronic high-frequency]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	1
Light source color	840 neutral white
Operating and Electrical	
Input Voltage	220 to 240 V


Power Consumption	21 W
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class II
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TCH128 1xTL5-21W/840 HF
Full product name	TCH128 1xTL5-21W/840 HF
Full product code	871155914853399
Order code	910502537518

Pentura Mini

Material Nr. (12NC)	910502537518
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559148533
Numerator - Packs per outer box	16

EAN/UPC - Case	8711559804538
----------------	---------------

Dimensional drawing



Product	A
TCH128 1xTL5-21W/840 HF	923 mm

