



Zadora, fixed

QBS570 1xHAL-R40-50WGZ10 K 230V II ALU

1, 50 W, GZ10, 230 V, Safety class II, Aluminum

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

Product data

General Information	
Cap-Base	GZ10 [GZ10]
Gear	-
Lighting Technology	LED
Value ladder	Value
Light Technical	
Number of light sources	1
Luminaire light beam spread	40°
Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	50 W
Temperature	
Ambient temperature range	-10 to +35 °C

Controls and Dimming	
Driver/power unit/transformer	-
Mechanical and Housing	
Housing Color	Aluminum
Overall length	37 mm
Overall width	225 mm
Overall height	225 mm
Dimensions (Height x Width x Depth)	225 x 225 x 37 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II
Product Data	
Order product name	QBS570 1xHAL-R40-50WGZ10 K 230V II ALU
Full product name	QBS570 1xHAL-R40-50WGZ10 K 230V II ALU
Full product code	871155957307600
Order code	910502540318

Zadora, fixed

Material Nr. (12NC)	910502540318
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559573076
Numerator - Packs per outer box	1

EAN/UPC - Case	8711559573076
----------------	---------------

Dimensional drawing

