



Zadora, adjustable

QBD570 1xHAL-R40-50WGZ10 K 230V II WH

1, 50 W, GZ10, 230 V, Safety class II, White

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

Product data

General Information		Controls and Dimming	
Cap-Base	GZ10 [GZ10]	Driver/power unit/transformer	-
Gear	-		
Lighting Technology	LED	Mechanical and Housing	
Value ladder	Value	Housing Color	White
		Overall length	75 mm
		Overall width	322 mm
		Overall height	322 mm
		Dimensions (Height x Width x Depth)	322 x 322 x 75 mm
Light Technical		Approval and Application	
Number of light sources	1	Ingress protection code	IP20 [Finger-protected]
Luminaire light beam spread	40°	Mech. impact protection code	IK00 [No protection]
		Protection class IEC	Safety class II
Operating and Electrical		Product Data	
Input Voltage	230 V	Order product name	QBD570 1xHAL-R40-50WGZ10 K 230V II WH
Line Frequency	50 to 60 Hz	Full product name	QBD570 1xHAL-R40-50WGZ10 K 230V II WH
Input Frequency	50 to 60 Hz	Full product code	871155957312000
Power Consumption	50 W	Order code	910502540418
Connection	-		
Temperature			
Ambient temperature range	-10 to +35 °C		

Zadora, adjustable

Material Nr. (12NC)	910502540418
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559573120
Numerator - Packs per outer box	1

EAN/UPC - Case	8711559573120
----------------	---------------

Dimensional drawing

