



# Zadora, adjustable

## QBD570 1xHAL-R40-50WGZ10 K 230V II ALU

ZADORA, 1, 50 W, GZ10, 230 V, Safety class II, Aluminum

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

### Product data

| General Information         |  | Temperature                         |                         |
|-----------------------------|--|-------------------------------------|-------------------------|
| Cap-Base                    | GZ10 [GZ10]                            | Ambient temperature range           | -10 to +35 °C           |
| Gear                        | -                                      |                                     |                         |
| Product family code         | QBD570 [ZADORA]                        | Controls and Dimming                |                         |
| Lighting Technology         | LED                                    | Driver/power unit/transformer       | -                       |
| Value ladder                | Value                                  |                                     |                         |
| Light Technical             |  | Mechanical and Housing              |                         |
| Number of light sources     | 1                                      | Housing Color                       | Aluminum                |
| Luminaire light beam spread | 40°                                    | Overall length                      | 75 mm                   |
|                             |  | Overall width                       | 322 mm                  |
|                             |  | Overall height                      | 322 mm                  |
|                             |  | Dimensions (Height x Width x Depth) | 322 x 322 x 75 mm       |
| Operating and Electrical    |  | Approval and Application            |                         |
| Input Voltage               | 230 V                                  | Ingress protection code             | IP20 [Finger-protected] |
| Line Frequency              | 50 to 60 Hz                            | Mech. impact protection code        | IK00 [No protection]    |
| Input Frequency             | 50 to 60 Hz                            | Protection class IEC                | Safety class II         |
| Power Consumption           | 50 W                                   |                                     |                         |
| Connection                  | -                                      |                                     |                         |
| Product Data                |  |                                     |                         |
| Order product name          | QBD570 1xHAL-R40-50WGZ10 K 230V II ALU |                                     |                         |

## Zadora, adjustable

|                               |  |
|-------------------------------|--|
| Full product name             | QBD570 1xHAL-R40-50WGZ10 K 230V II ALU |
| Full product code             | 871155957315100                        |
| Order code                    | 910502540718                           |
| Material Nr. (12NC)           | 910502540718                           |
| Numerator - Quantity Per Pack | 1                                      |

|                                 |               |
|---------------------------------|---------------|
| EAN/UPC - Product/Case          | 8711559573151 |
| Numerator - Packs per outer box | 1             |
| EAN/UPC - Case                  | 8711559573151 |

### Dimensional drawing

