



Pentura Mini CC

TCH129 1xTL5-28W/830 HF

1, TL5, 28 W, 830 warm white, Electronic high-frequency


Pentura Mini CC TCH129 is an ultra-slim decorative batten for domestic applications. This cost-effective, ready-to-install solution offers the energy-saving benefits of miniature fluorescent lamp technology coupled with lightweight electronics and a patented internal reflector for improved lighting performance. Pentura Mini CC TCH129 is fitted with plug-and-socket connections and an on/off switch for individual operation over worktops and workstations in the home, home office and recreational environments.

Product data

| General Information | |
|--------------------------|---|
| Lamp family code | TL5 [TL5] |
| Gear | HF [Electronic high-frequency] |
| CE mark | Yes |
| Flammability mark | For mounting on normally flammable surfaces |
| Glow-wire test | Temperature 850 °C, duration 5 s |
| Light Technical | |
| Number of light sources | 1 |
| Light source color | 830 warm white |
| Operating and Electrical | |
| Input Voltage | 220 to 240 V |
| Power Consumption | 28 W |
| Mechanical and Housing | |
| Overall length | 1,205 mm |

| Approval and Application | |
|---------------------------------|-------------------------|
| Ingress protection code | IP20 [Finger-protected] |
| Protection class IEC | Safety class II |
| Application Conditions | |
| Suitable for random switching | Not applicable |
| Product Data | |
| Order product name | TCH129 1xTL5-28W/830 HF |
| Full product name | TCH129 1xTL5-28W/830 HF |
| Full product code | 871155900878399 |
| Order code | 910502546918 |
| Material Nr. (12NC) | 910502546918 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711559008783 |
| Numerator - Packs per outer box | 16 |
| EAN/UPC - Case | 8711559804682 |

Dimensional drawing



| Product | A |
|-------------------------|----------|
| TCH129 1xTL5-28W/830 HF | 1,205 mm |

