



Tempo 3 RVP351

RVP351 SON-TPP250W K IC A

250 W, Asymmetrical

Tempo is a complete floodlighting range offering a wide choice of lamp types and symmetrical and asymmetrical reflectors. It is designed for general-purpose floodlighting, and is particularly suited to small- to medium-scale area or surface lighting. The Tempo series' compact housing guarantees optimum visual integration. Anodized-aluminum reflectors ensure a highly efficient beam distribution, while the nylon bolt caps feature a goniometric aiming device for easy adjustment and alignment. A universal mounting bracket allows ceiling, wall or surface mounting with a wide range of adjustment for both down- and uplighting. Tempo's all-weather construction is designed to make cleaning and servicing easy and fast. Access to the lamp and gear is simple, via the hinged front glass with its quick-release stainless-steel clips. All Tempo luminaires are RoHS-compliant.

Product data

| General Information | |
|------------------------------------|----------------------------------|
| Lamp family code | SON-TPP [SON-T PIA Plus] |
| Gear | CONV [Conventional] |
| Glow-wire test | Temperature 850 °C, duration 5 s |
| CE mark | Yes |
| ENEC mark | - |
| Warranty period | 1 years |
| EU RoHS compliant | Yes |
| Light Technical | |
| Upward light output ratio | 0 |
| Correlated Color Temperature (Nom) | 2000 K |
| Color rendering index (CRI) | 25 |
| Number of light sources | 1 |

| Light source color | 220 gold |
|-------------------------------|-------------------------------|
| Optical cover type | Flat glass |
| Optic type outdoor | Asymmetrical |
| Operating and Electrical | |
| Input Voltage | 230 V |
| Line Frequency | 50 Hz |
| Initial CLO power consumption | {NO} - W |
| End CLO power consumption | {NO} - W |
| Power Consumption | 250 W |
| Power Factor (Fraction) | 0.85 |
| Connection | Screw connection block 3-pole |
| Cable | - |

Tempo 3 RVP351

| | |
|---------------------------|-------------------|
| Temperature | |
| Ambient temperature range | -25 to +35 °C |
| Controls and Dimming | |
| Dimmable | No |
| Constant light output | No |
| Mechanical and Housing | |
| Housing Material | Aluminum die cast |
| Reflector material | Aluminum |
| Optic material | Aluminum |
| Optical cover material | Glass |
| Fixation material | Steel |
| Housing Color | Grey |
| Optical cover shape | Flat |
| Optical cover finish | Clear |
| Overall length | 428 mm |
| Overall width | 464 mm |
| Overall height | 146 mm |
| Effective projected area | 0.165 m² |

| | |
|-------------------------------------|--|
| Dimensions (Height x Width x Depth) | 146 x 464 x 428 mm |
| Approval and Application | |
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK07 [2 J reinforced] |
| Protection class IEC | Safety class I |
| Product Data | |
| Order product name | RVP351 SON-TPP250W K IC A |
| Full product name | RVP351 SON-TPP250W K IC A |
| Full product code | 871155914974500 |
| Order code | 910502548818 |
| Material Nr. (12NC) | 910502548818 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711559149745 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8711559149745 |

Dimensional drawing

