



TTX400 TL5, GGX550 louvers and optics

GGX555 49 M2

49 W

A wide range of different louvers and optics can be mounted in the multifunctional reflector GMX555. These attachments offer many possibilities to shield the lamps and therefore improve comfort. Each attachment is available in 1-lamp and 2-lamp versions. Changing the lamp remains simple and quick as the attachments are hinged to the GMX555. The attachments, optics and mirror inserts can only be used in combination with the functional reflector GMX555/GMX555 RS/GMX555 RP.

Product data

| Operating and Electrical | | Material Nr. (12NC) | |
|--------------------------|-----------------|---------------------------------|---------------|
| Power Consumption | 49 W | Numerator - Quantity Per Pack | 1 |
| Product Data | | EAN/UPC - Product/Case | 8711559684734 |
| Order product name | GGX555 49 M2 | Numerator - Packs per outer box | 5 |
| Full product name | GGX555 49 M2 | EAN/UPC - Case | 8711559684741 |
| Full product code | 871155968473499 | | |
| Order code | 910502747018 | | |