



Zadora, fixed

QBW163 1xHAL-MR50-35WGU5.3 12V WH

1, MASTER Line ES 50 mm, 35 W, GU5.3, 12 V, White

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

Product data

General Information	
Lamp family code	HAL-MR50 [MASTER Line ES 50 mm]
Cap-Base	GU5.3 [GU5.3]
Service tag	Yes
Value ladder	Value
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	1
Operating and Electrical	
Input Voltage	12 V
Power Consumption	35 W
Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP44 [Wire-protected, splash-proof]
Protection class IEC	Safety class III
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	QBW163 1xHAL-MR50-35WGU5.3 12V WH
Full product name	QBW163 1xHAL-MR50-35WGU5.3 12V WH
Full product code	871155900808099
Order code	910502846518
Material Nr. (12NC)	910502846518
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559008080
Numerator - Packs per outer box	50
EAN/UPC - Case	8711559008165