



Impala TBS160

TBS160 4xTL-D18W/840 HFS C6-1000 SC

IMPALA, 4, MASTER TL-D, 18 W, 840 neutral white, HF Standard, High-gloss optic double parabolic, limit 1000 cd

Impala TBS160 is a functional recessed luminaire for 2, 3 or 4 TL-D fluorescent lamps. It offers a wide range of optics as well as a prismatic plate. The optics/plate are fitted to the housing by means of a clip for easy installation and maintenance. An external connection system enables the mains connection to be made without opening the luminaire. The luminaire fits in visible profile ceilings as standard and, using accessories, in concealed and plaster ceilings.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HFS [HF Standard]
Product family code	TBS160 [IMPALA]
Embedded control	-
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 960 °C, duration 5 s
Light Technical	
Number of light sources	4
Light source color	840 neutral white
Optic type	High-gloss optic double parabolic, limit 1000 cd
Optical cover type	-

Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	18 W
Connection	-
Cable	-

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Application Conditions	
Suitable for random switching	Not applicable

Product Data	
Order product name	TBS160 4xTL-D18W/840 HFS C6-1000 SC
Full product name	TBS160 4xTL-D18W/840 HFS C6-1000 SC

Impala TBS160

Full product code	871155969735200
Order code	910503303618
Material Nr. (12NC)	910503303618
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559697352

Numerator - Packs per outer box	1
EAN/UPC - Case	8711559697352

Dimensional drawing

