



# Latina FBH024

## FBH024 2xPL-C/4P18W/830 K HF WH RG

Latina, 2, MASTER PL-C 4 Pin, 18 W, 830 warm white, Electronic high-frequency, White

Latina is a recessed downlight for compact fluorescent PL-C lamps, with spring fasteners for easy and quick installation. Square and round models are available. Latina comes in ready-to-install kit versions, including lamps and pre-connected separate gearbox. The round models are available in glass versions (frosted glass or clear decorative glass) or in open versions. For the open versions, the same glass designs are available as accessories (to be ordered separately). The square versions are always with glass.

### Product data

General Information	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Gear	HF [Electronic high-frequency]
Product family code	FBH024 [Latina]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 960 °C, duration 5 s
Light Technical	
Number of light sources	2
Light source color	830 warm white
Operating and Electrical	
Input Voltage	230 to 240 V
Power Consumption	18 W

Connection	-
Mechanical and Housing	
Housing Color	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	FBH024 2xPL-C/4P18W/830 K HF WH RG
Full product name	FBH024 2xPL-C/4P18W/830 K HF WH RG
Full product code	871794388500899

Latina FBH024

Order code	910503633918
Material Nr. (12NC)	910503633918
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943885008

Numerator - Packs per outer box	4
EAN/UPC - Case	8717943885336

Dimensional drawing

