



# Latina FBH024

## FBH024 2xPL-C/4P18W/840 K HF WH RG

2, MASTER PL-C 4 Pin, 18 W, 840 neutral white, Electronic high-frequency, White

Latina is a recessed downlight for compact fluorescent PL-C lamps, with spring fasteners for easy and quick installation. Square and round models are available. Latina comes in ready-to-install kit versions, including lamps and pre-connected separate gearbox. The round models are available in glass versions (frosted glass or clear decorative glass) or in open versions. For the open versions, the same glass designs are available as accessories (to be ordered separately). The square versions are always with glass.

### Product data

General Information		Mechanical and Housing	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]	Housing Color	White
Gear	HF [Electronic high-frequency]	Approval and Application	
CE mark	Yes	Ingress protection code	IP20 [Finger-protected]
Flammability mark	For mounting on normally flammable surfaces	Protection class IEC	Safety class I
Glow-wire test	Temperature 960 °C, duration 5 s	Application Conditions	
Light Technical		Suitable for random switching	Not applicable
Number of light sources	2	Product Data	
Light source color	840 neutral white	Order product name	FBH024 2xPL-C/4P18W/840 K HF WH RG
Operating and Electrical		Full product name	FBH024 2xPL-C/4P18W/840 K HF WH RG
Input Voltage	230 to 240 V	Full product code	871794388502299
Power Consumption	18 W	Order code	910503634118
Connection	-	Material Nr. (12NC)	910503634118

Latina FBH024

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943885022
Numerator - Packs per outer box	4

EAN/UPC - Case	8717943885350
----------------	---------------

Dimensional drawing

