



Latina FBH024

FBH024 2xPL-C/4P18W/840 K HF WH FRG

2, MASTER PL-C 4 Pin, 18 W, 840 neutral white, Electronic high-frequency, White

Latina is a recessed downlight for compact fluorescent PL-C lamps, with spring fasteners for easy and quick installation. Square and round models are available. Latina comes in ready-to-install kit versions, including lamps and pre-connected separate gearbox. The round models are available in glass versions (frosted glass or clear decorative glass) or in open versions. For the open versions, the same glass designs are available as accessories (to be ordered separately). The square versions are always with glass.

Product data

General Information	
Lamp family code	PL-C/4P [MASTER PL-C 4 Pin]
Gear	HF [Electronic high-frequency]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 960 °C, duration 5 s
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Operating and Electrical	
Input Voltage	230 to 240 V
Power Consumption	18 W
Connection	-

Mechanical and Housing	
Housing Color	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	FBH024 2xPL-C/4P18W/840 K HF WH FRG
Full product name	FBH024 2xPL-C/4P18W/840 K HF WH FRG
Full product code	871794388503999
Order code	910503634218
Material Nr. (12NC)	910503634218

Latina FBH024

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943885039
Numerator - Packs per outer box	4

EAN/UPC - Case	8717943885367
----------------	---------------

Dimensional drawing

