



TBS165

TBS165 G 4xTL5-14W/830 HFS C3 PIP SC

4, TL5, 14 W, 830 warm white, HF Standard, High-gloss mirror matt aluminum louver, Push-in connector and pull relief

Designed to address the need for energy-efficient basic lighting, the TBS165 luminaire makes it possible to save energy by replacing outdated electromagnetic installations with Philips TL5 technology. Featuring innovative dedicated TL5 optics, a choice of ballasts, sensors (presence detection, daylight regulation) and emergency lighting, the TBS165 range can be used for general lighting in a wide variety of applications, including offices, corridors, schools and shops (supermarkets, DIY). Combining high-frequency gear, sensors and MASTER TL5 lamps, it allows substantial energy savings. The low-height recessed luminaire fits in exposed ceilings. Conveniently, it does not have to be opened, as it has pre-installed lamps and can be connected from the outside.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFS [HF Standard]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	4
Light source color	830 warm white
Optic type	High-gloss mirror matt aluminum louver

Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	14 W
Connection	Push-in connector and pull relief
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable

TBS165

Product Data	
Order product name	TBS165 G 4xTL5-14W/830 HFS C3 PIP SC
Full product name	TBS165 G 4xTL5-14W/830 HFS C3 PIP SC
Full product code	871794388804700
Order code	88804700
Material Nr. (12NC)	910503652018

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943888047
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943888047

Dimensional drawing

