



# CoreLine recessed

## RC120B LED37S/840 PSU W30L120

Coreline Recessed, LED Module, system flux 3700 lm, 840 neutral white, Power supply unit (On/Off)

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Recessed range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch. In addition, Coreline Recessed also provides the option of advanced connectivity and is ready to be connected to IoT based software applications such as Interact Pro.

### Warnings and Safety

- The product is IPX0 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void

### Product data

General Information		
Lamp family code	LED37S [LED Module, system flux 3700 lm]	
Cap base	- [-]	
Light source replaceable	No	
Number of gear units	Unit	
Gear	EB [Electronic]	
Driver included	Yes	
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Product family code	RC120B [Coreline Recessed]	
Lighting Technology	LED	
Value ladder	Performance	
CE mark	Yes	
Warranty period	3 years + 2 years upon registration	
Flammability mark	For mounting on normally flammable surfaces	

## CoreLine recessed

ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 30 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	3,700 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	93 lm/W
Colour rendering index (CRI)	≥80
Light source colour	840 neutral white
Optic type	Wide beam
Optical cover type	Polycarbonate linear satinised
Luminaire light beam spread	86°
Unified Glare Rating (CEN)	Not applicable

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	8 A
Inrush time	0.06 ms
Power Consumption	34.2 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

### Mechanical and Housing

Housing material	Steel
Reflector material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate

Fixation material	-
Housing Colour	White
Optical cover/lens finish	Textured
Overall length	1,197 mm
Overall width	297 mm
Overall height	32 mm
Dimensions (height x width x depth)	32 x 297 x 1197 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L75

### Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Yes

### Product Data

Order product name	RC120B LED37S/840 PSU W30L120
Full product name	RC120B LED37S/840 PSU W30L120
Full EOC	871794389757500
Order code	89757500
Material no. (12 NC)	910503695318
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514183391
Numerator – packs per outer box	1
EAN/UPC – Case	8717943897575

## CoreLine recessed

### Dimensional drawing

