



ColorBurst Compact Powercore



ColorBurst Compact Powercore, 8° (No Spread Lens), Black Housing, UL/cUL/CE, Architectural

ColorBurst Compact Powercore, 8° (No Spread Lens), Black Housing, UL/cUL/CE, Architectural

ColorBurst Compact Powercore is a high-output, exterior-rated LED lighting luminaire designed for accent and site lighting. Architectural and landscape luminaires deliver full-color light output of up to 498 lumens to support a range of uplighting, floodlighting, and decorative lighting applications.

Product data

General information		Input Frequency	
Number of light sources	12 pcs	50 to 60 Hz	
Lamp family code	LED-HB [LED High Brightness]	Controls and dimming	
Light source color	Red, green and blue	Dimmable	
Light source replaceable	No	No	
Driver included	No	Mechanical and housing	
Luminaire light beam spread	8°	Housing configuration	
Protection class IEC	Safety class I	Basic version	
CE mark	CE mark	Color	
UL mark	UL mark	Black	
Optic type outdoor	Narrow beam angle 8°	Approval and application	
Operating and electrical		Ingress protection code	
Input Voltage	100 to 240 V	IP66 [Dust penetration-protected, jet-proof]	
		Energy Efficiency Class	
		G	
		Vibration Standard	
		Complies with ANSI C136.31, 3G	
		FCC mark	
		FCC Class A	
		Vibration Rating	
		Complies with ANSI C136.31, 3G	


ColorBurst Compact Powercore

EPREL Registration Number	1012747
Initial performance (IEC compliant)	
Initial input power	17.5 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25°C Reported	100,000
Lumen Maintenance 50% at 50°C Reported	90,000
Product data	
Full product code	871794388483499
Order product name	BCP462 12xLED-HB/RGB 100-240V BK

EAN/UPC - Product	8717943884834
Order code	123-000019-04
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	910503701818
Net Weight (Piece)	3.500 kg
Catalog Number	123-000019-04
Catalog Number Description	ColorBurst Compact Powercore, 8° (No Spread Lens), Black Housing, UL/cUL/CE, Architectural



Dimensional drawing



BCP462 12xLED-HB/RGB 100-240V BK

