



ArchiPoint iColor

ArchiPoint iColor Powercore, Translucent Dome Lens with Conduit Mounting Base, M25 (metric size conduit)

ArchiPoint iColor Powercore, Translucent Dome Lens with Conduit Mounting Base, M25 (metric size conduit)

ArchiPoint iColour Powercore is a daylight-visible, exterior-rated LED point of light ideally suited for a range of direct-view and beacon applications, as well as for accent applications such as path and marker lighting. These versatile low-profile fixtures display large-scale video, graphics, and intricately designed dynamic effects in a host of settings, including architectural, retail, and entertainment installations. ArchiPoint iColour Powercore offers high-intensity output with the efficiency and cost-effectiveness of Powercore technology in a rugged aluminum housing. Powercore delivers line voltage and data to fixtures over a single cable, dramatically simplifying installation and lowering total system cost.

Product data

General information		Accessory PFC	
Lamp family code	LED-HB [LED High Brightness]	ZCP780	
Lamp colour code	Red, green and blue		
Light source replaceable	No		
Driver included	Yes		
Optical cover/lens type	TSDM [Transparent dome]		
Luminaire light beam spread	150°		
Protection class IEC	Safety class I (I)		
CE mark	CE mark		
UL mark	UL mark		
CCC mark	-		
Operating and electrical			
Input Voltage	100 to 240 V		
Input frequency	50 to 60 Hz		
Controls and dimming			
Dimmable	No		
Mechanical and housing			
Housing material	Aluminum die-cast		
Optic material	Polycarbonate		

Colour	Silver
--------	--------

Approval and application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Energy Efficiency Class	G
Mech. impact protection code	IK10 [20 J vandal-resistant]
Vibration standard	Complies with ANSI C136.31, 3G
FCC mark	FCC Class A
Vibration rating	Complies with ANSI C136.31, 3G
	953156

Initial performance (IEC compliant)

Initial luminous flux (system flux)	501 lm
Initial LED luminaire efficacy	17.6 lm/W
Initial input power	25 W

Over time performance (IEC compliant)

Lumen Maintenance 50% at 25 °C	100000
Reported	
Lumen Maintenance 50% at 50 °C	70000
Reported	
Lumen Maintenance 70% at 25 °C	70000
Reported	

Lumen Maintenance 70% at 50 °C	40000
Reported	

Application conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product data


Full product code	871829138149599
Order product name	BCP780 LED-HB/RGB 100-240V TS DM SI CE UL
EAN/UPC – product	8718291381495
Order code	123-000022-00
SAP numerator – quantity per pack	1
Numerator – packs per outer box	4
SAP material	910503702579
Net Weight (Piece)	1.500 kg
Commercial Code	123-000022-00
Commercial Code	ArchiPoint iColor Powercore, Translucent Dome Lens with Conduit Mounting Base, M25 (metric size conduit)




Dimensional drawing




BCP780 LED-HB/RGB 100-240V TS DM SI CE UL



BCP780 LED-HB/RGB 100-240V TS DM SI CE UL




BCP780 LED-HB/RGB 100-240V TS DM SI CE UL



BCP780 LED-HB/RGB 100-240V TS DM SI CE UL

Dimensional drawing



BCP780 LED-HB/RGB 100-240V TSDM SI CE UL

